





































































ELECTRONIC SINGLE BREAST PUMPS
ELECTRONIC DOUBLE BREAST PUMPS

								
MODEL	NENO UNO	NENO ANGELO	NENO BELLA	NENO DUE	NENO CAMINO	NENO BUENO	NENO BELLA TWIN	NENO MARE
Work modes								
Levels of stimulation	6	9	6	5	5	5	6	6
Levels of expression	9	9	9	9	9	9	9	9
Levels of mixed mode	-	9	-	-	5	-	-	-
Work time								
Automatic power off	after 30 minutes	after 30 minutes	after 30 minutes	after 30 minutes	after 30 minutes	after 30 minutes	after 30 minutes	after 30 minutes
Charging time	about 120 minutes	about 120 minutes	about 120 minutes	about 120 minutes	about 120 minutes	about 120 minutes	about 120 minutes	about 120 minutes
Charging port	 USB-C	 USB-C	 USB-C	 USB-C	 USB-C	 USB-C	 USB-C	 USB-C
Battery	Lithium-ion 3.7 V 1400 mAh	Lithium-ion 3.7 V 1400 mAh	Lithium-ion 3.7 V 1400 mAh	Lithium-ion 3.7 V 2000 mAh	Lithium-ion 3.7 V 1400 mAh	Lithium-ion 3.7 V 2000 mAh	Lithium-ion 3.7 V 1400 mAh	Lithium-ion 3.7 V 2000 mAh
Cross connection	-	-	-					
Number of inputs to the pump	-	-	1	2	1	2	1	2
Weight	300 g	392 g	417 g	785 g	706 g	790 g	733 g	748 g
Bottle	 150 ml PP material BPA FREE	 180 ml PP material BPA FREE	 150 ml PP material BPA FREE	 150 ml PP material BPA FREE	 180 ml PPSU material BPA FREE	 180 ml PPSU material BPA FREE	 150 ml PP material BPA FREE	 150 ml PP material BPA FREE
Additional valve								
Additional bottle cap								
Storage bag			PLASTIC CASE					
Package contents	Breast pump, milk bottle, bottle stand, 2 x bottle cap, 2 x valve, suction bowl, bottle teat, breast shield + dust cover, USB-C cable, user's manual	Breast pump, milk bottle, bottle cap, 2 x bottle cap, 2 x valve, suction bowl, bottle teat, breast shield + dust cover, USB-C cable, user's manual	Breast pump, milk bottle, bottle stand, 2 x bottle cap, 2 x valve, suction bowl, bottle teat, breast shield + dust cover, USB-C cable, user's manual	Breast pump, 2 x milk bottle, 2 x bottle stand, 2 x bottle cap, 4 x valve, 2 x suction bowl, 2 x bottle teat, breast shields + dust covers, 2 x silicone cord, USB-C cable, user's manual	Breast pump, 2 x PREMIUM milk bottles, 2 x bottle stand, 2 x bottle cap, 4 x valve, 2 x suction bowl, 2 x bottle teat, breast shields + dust covers, silicone cord, USB-C cable, user's manual	Breast pump, 2 x PREMIUM milk bottles, 2 x bottle stand, 2 x bottle cap, 4 x valve, 2 x suction bowl, 2 x bottle teat, breast shields + dust covers, 2 x silicone cord, USB-C cable, user's manual	Breast pump, 2 x milk bottle, 2 x bottle stand, 2 x bottle cap, 4 x valve, 2 x suction bowl, 2 x bottle teat, breast shields + dust covers, 2 x silicone cord, USB-C cable, user's manual	Breast pump, 2 x milk bottle, 2 x bottle stand, 2 x bottle cap, 4 x valve, 2 x suction bowl, 2 x bottle teat, breast shields + dust covers, 2 x silicone cord, USB-C cable, user's manual